

1920 x 1200
WUXGA



Display Features & Benefits

- ▶ 6U rackmount 17" widescreen LCD
- ▶ 1920 x 1200 native **WUXGA** Ultra high resolution
- ▶ PIP & Picture by Picture viewing efficiency
- ▶ Green LED-backlit panel technology
- ▶ 8-bit colors
- ▶ Built-in HDMI, DVI-D, VGA, S-Video + BNC & Audio

Options

- 3G / HD / SD-SDI Broadcast-grade input
- **MC** Multi-display control solution
- 17" Touchscreen : Capacitive, Resistive
- DC power : 12V / 24V / 48V / 110 ~ 125V
- MIL-type or lockable connector



Basic I/O : VGA + DVI-D + HDMI + BNC + S-Video + audio
Options : SDI, USB for touchscreen & DC power

Specifications

• **LCD Panel**

- Size (diagonal) : 17.1" widescreen TFT
- Max resolution : 1920 x 1200
- Brightness (cd/m2) : 210
- Backlight : LED
- Colors : 16.7 M, 8-bit
- Contrast ratio (typ) : 600 : 1
- Viewing angle (H/V) : 130° x 110°
- Active area (mm) : 367 x 230
- MTBF (hrs) : 20,000
- Signal input : HDMI / DVI-D / VGA / S-Video / BNC

• **Speaker :**

Built-in Dual Stereo Speakers
2W x 2

• **Power Input :**

Auto-sensing 100 to 240VAC, 50 / 60Hz

• **Power Consumption**

- Screen on : Max. 34W
- Power saving mode : Max. 4W
- Power button on : Max. 1W

• **Environmental**

- Operating temperature : 0 to 55°C degree
- Storage temperature : -20 to 60°C degree
- Operating humidity : 20~90%, non-condensing
- Storage humidity : 5 ~90%, non-condensing
- Operating altitude : 16,000 ft
- Non-operating altitude : 40,000 ft
- Shock : 10G acceleration (11ms duration)
- Vibration : 5~500Hz 1G RMS random vibration

• **Casing Color :**

Black (RAL 9005)

• **Regulatory**

- Safety : FCC & CE certified
- Environmental : RoHS2 & REACH compliant

• **Weight**

Net : 4.2 kgs / 9.2 lbs

• **Dimensions**

Product : 480 x 48 x 266 mm / 18.9 x 1.9 x 10.5 inch

Diagrams (mm)

