



1920 x 1200
WUXGA




Drawer Features & Display Benefits

- ▶ 1U 17" widescreen LCD drawer with DVI-D / VGA input
- ▶ 1920 x 1200 native **WUXGA** Ultra high resolution
- ▶ Support **Full HD** with 1080p resolution
- ▶ PIP & Picture by Picture viewing efficiency
- ▶ Green LED-backlit panel technology
- ▶ 8-bit colors
- ▶ Enhanced aesthetics with molded front panel and two point lock
- ▶ Short depth design of 480mm (18.9") only

Options

- 3G / HD / SD-SDI Broadcast-grade input
- 17" Touchscreen : Capacitive, Resistive
- HDMI or Audio input
- DC power : 12V / 24V / 48V / 110 ~ 125V



Basic I/O : VGA and DVI-D

**Options : HDMI, Audio
SDI, USB for touchscreen**

** For the above options, casing depth will be extended from 480mm (18.9") to 530mm (20.9")

Specifications

• LCD Panel

- Size (diagonal) : 17.1" widescreen TFT
- Max resolution : 1920 x 1200
- Brightness (cd/m2) : 210
- Backlight : LED
- Colors : 16.7 M, 8-bit
- Contrast ratio (typ) : 600 : 1
- Viewing angle (H/V) : 130° x 110°
- Active area (mm) : 367 x 230
- MTBF (hrs) : 20,000
- Signal input : VGA or DVI-D

• Speaker :

Built-in Dual Stereo Speakers
(option) 2W x 2

• Power Input :

Auto-sensing 100 to 240VAC, 50 / 60Hz

• Power Consumption

- Screen on : Max. 34W
- Power saving mode : Max. 4W
- Power button on : Max. 1W

• Environmental

- Operating temperature : 0 to 55°C degree
- Storage temperature : -20 to 60°C degree
- Operating humidity : 20~90%, non-condensing
- Storage humidity : 5 ~90%, non-condensing
- Operating altitude : 16,000 ft
- Non-operating altitude : 40,000 ft
- Shock : 10G acceleration (11ms duration)
- Vibration : 5~500Hz 1G RMS random vibration

• Casing Color :

Black (RAL 9005)

• Regulatory

- Safety : FCC & CE certified
- Environmental : RoHS2 & REACH compliant

• Weight

Net : 11 kgs / 24.2 lbs

• Dimensions

Product : 441.6 x 480 x 44 mm / 17.4 x 18.9 x 1.73 inch

Diagrams (mm)

