

## SERVER CABINETS - 36" DEPTH

MADE IN THE USA



The 36" depth Server Cabinets are packed with some of the most popular rack features at a price virtually anyone can afford. The cabinets feature laser knockouts allowing you to install fans, while removable slots provide numerous cable routing options. Built with a 36" depth, these cabinets are suitable for network servers, battery backups, switching banks, and other larger network equipment. To suit your particular network install, numerous door configurations are available (including glass, solid, vented, and convex doors), and we even offer cabinets without doors and/or without side panels. When you need a low cost solution packed with features, these Server Cabinets deliver!

- 1300 lb. weight capacity (800 lbs. on casters)
- Preinstalled casters and levelers
- Includes two sets of adjustable cage nut style mounting rails
- Removable locking side panels
- Top includes removable laser knockouts
- 19" EIA 310-D compliant
- Made in the USA

### FEATURES

**Easy Installation** - Casters and levelers are preinstalled to allow you to easily move and load your system into the desired location. (Rack hardware not included.)

**Removable Cable Access Panels** - The top of the server cabinet includes removable laser knockouts for cable access and added versatility.

**Locking, Removable Side Panels** - For a completely different look, the side panels are both removable and lockable giving you the option to create the cabinet that best suits your needs.

**Adjustable Rails** - Includes two sets of adjustable, vertical rails which extend to a maximum depth of 36" for versatile mounting options.

**Secured System** - Both doors are equipped with locks to help protect and secure your valuable equipment.

**GLASS  
DOOR**

**SOLID  
DOOR**

**VENTED  
DOOR**

**CONVEX  
DOOR**

**NO DOORS/NO  
SIDE PANELS**

**NO  
DOORS**



## 22U SPECIFICATIONS

Door 1	Door 2	Part Number	Dimensions
Glass	Vented	CR1203	24" W x 37.72" D x 45.50" H
Glass	Solid	CR1203-G/S	24" W x 37.72" D x 45.50" H
Convex	Glass	CR1203-C/G	24" W x 38.22" D x 45.50" H
Glass	Glass	CR1203-G/G	24" W x 37.72" D x 45.50" H
Solid	Convex	CR1203-S/C	24" W x 38.22" D x 45.50" H
Convex	Convex	CR1203-C/C	24" W x 38.22" D x 45.50" H
Solid	Vented	CR1203-S/V	24" W x 37.72" D x 45.50" H
Vented	Vented	CR1203-V/V	24" W x 37.72" D x 45.50" H
Solid	Solid	CR1203-S/S	24" W x 37.72" D x 45.50" H
Convex	Vented	CR1203-C/V	24" W x 38.22" D x 45.50" H
No Doors/No Side Panels		CR1203-A	24" W x 37.72" D x 45.50" H
No Doors		CR1203-C	24" W x 37.72" D x 45.50" H

## 27U SPECIFICATIONS

Door 1	Door 2	Part Number	Dimensions
Glass	Vented	CR1205	24" W x 37.72" D x 54.25" H
Glass	Solid	CR1205-G/S	24" W x 37.72" D x 54.25" H
Convex	Glass	CR1205-C/G	24" W x 38.22" D x 54.25" H
Glass	Glass	CR1205-G/G	24" W x 37.72" D x 54.25" H
Solid	Convex	CR1205-S/C	24" W x 38.22" D x 54.25" H
Convex	Convex	CR1205-C/C	24" W x 38.22" D x 54.25" H
Solid	Vented	CR1205-S/V	24" W x 37.72" D x 54.25" H
Vented	Vented	CR1205-V/V	24" W x 37.72" D x 54.25" H
Solid	Solid	CR1205-S/S	24" W x 37.72" D x 54.25" H
Convex	Vented	CR1205-C/V	24" W x 38.22" D x 54.25" H
No Doors/No Side Panels		CR1205-A	24" W x 37.72" D x 54.25" H
No Doors		CR1205-C	24" W x 37.72" D x 54.25" H

## 37U SPECIFICATIONS

Door 1	Door 2	Part Number	Dimensions
Glass	Vented	CR1207	24" W x 37.72" D x 71.75" H
Glass	Solid	CR1207-G/S	24" W x 37.72" D x 71.75" H
Convex	Glass	CR1207-C/G	24" W x 38.22" D x 71.75" H
Glass	Glass	CR1207-G/G	24" W x 37.72" D x 71.75" H
Solid	Convex	CR1207-S/C	24" W x 38.22" D x 71.75" H
Convex	Convex	CR1207-C/C	24" W x 38.22" D x 71.75" H
Solid	Vented	CR1207-S/V	24" W x 37.72" D x 71.75" H
Vented	Vented	CR1207-V/V	24" W x 37.72" D x 71.75" H
Solid	Solid	CR1207-S/S	24" W x 37.72" D x 71.75" H
Convex	Vented	CR1207-C/V	24" W x 38.22" D x 71.75" H
No Doors/No Side Panels		CR1207-A	24" W x 37.72" D x 71.75" H
No Doors		CR1207-C	24" W x 37.72" D x 71.75" H

## 42U SPECIFICATIONS

Door 1	Door 2	Part Number	Dimensions
Glass	Vented	CR1209	24" W x 37.72" D x 80.50" H
Glass	Solid	CR1209-G/S	24" W x 37.72" D x 80.50" H
Convex	Glass	CR1209-C/G	24" W x 38.22" D x 80.50" H
Glass	Glass	CR1209-G/G	24" W x 37.72" D x 80.50" H
Solid	Convex	CR1209-S/C	24" W x 38.22" D x 80.50" H
Convex	Convex	CR1209-C/C	24" W x 38.22" D x 80.50" H
Solid	Vented	CR1209-S/V	24" W x 37.72" D x 80.50" H
Vented	Vented	CR1209-V/V	24" W x 37.72" D x 80.50" H
Solid	Solid	CR1209-S/S	24" W x 37.72" D x 80.50" H
Convex	Vented	CR1209-C/V	24" W x 38.22" D x 80.50" H
No Doors/No Side Panels		CR1209-A	24" W x 37.72" D x 80.50" H
No Doors		CR1209-C	24" W x 37.72" D x 80.50" H