

New




S-Video + BNC



Touchscreen - USB



DVI-D



Touchscreen - Serial



DC Power



Audio



**With touchscreen option, the height of LCD1U19-014 will be changed from 1U to 1.5U

Options

- 
AV
BNC + S-Video
- 
DVI
DVI-D
- 
DC
DC Power
- 
Touch Screen
- 
Audio
- 
QD
Quad Display

Drawer Features & Options

- 1U rackmount LCD drawer with 19" widescreen LCD
- Quad display option
- Touchscreen option
- 12V, 24V and 48V DC power options
- AV + BNC, Audio and DVI-D options

LCD Drawer Benefits

- ▶ 19" widescreen LCD with 1440 x 900 high resolution
- ▶ Sliding LCD allowing LCD to remain open when the rack door is closed
- ▶ Enhanced aesthetics with new molded front panel and two point lock

Monitor  Grade A Wide 19" industrial TFT LCD panel

- 19" 1440 x 900 LCD with 300 nit brightness and 1000:1 contrast ratio typical

Ordering Information

Model	LCD1U19-014
-------	-------------

Dimensions

Model	Product Dimension (W x D x H)	Net Weight
LCD1U19-014	442 x 650 x 44 mm 17.4 x 25.6 x 1.73 inch	13 kg / 29 lbs

Diagram

Unit : mm

