

# LCD1U-17012 / -15013 1U Rackmount 17" / 15" LCD Drawer



LCD1U17-012



LCD1U15-012

## FEATURES

- ◆ 1 rack unit high (1.75").
- ◆ 15" or 17" active matrix TFT LCD display.
- ◆ Display securely held in closed position.
- ◆ TFT surface protected by Lexan™ shield.
- ◆ Attaches directly to a standard VGA card.
- ◆ Display powers off when in closed position.
- ◆ 15" 16.7M Colors, 1024 x 768 maximum resolution.
- ◆ 17" 16.7M Colors, 1280 x 1024 maximum resolution.
- ◆ Wide viewing angle, high brightness and contrast.
- ◆ 18" Ball Bearing slides with extensions included.
- ◆ Recessed front panel handle fits behind rack doors.

## OPTIONS

**Color choice of light gray or black.**  
**Front panel retaining screws.**  
**Front panel lock (locks unit in rack).**  
**Telco rack (2 post) mounting brackets.**

## GENERAL SPECIFICATIONS

### Dimensions:

19.0" (W) x 1.75" (H) x 19.0" (D)

### Weight:

25 lbs

### Power (TFT Display):

90 - 260 VAC, 50/60 Hz.  
60 Watts maximum

### On-Screen Controls:

Brightness, Contrast, Horizontal & Vertical  
Position, Auto Adjust, OSD H & V Position, Load  
and Save Values

### Plug & Play:

DDC1 and DDC2B

### Temperature:

Operating: 0°C to 50°C  
Storage: -20°C to 60°C

### Humidity:

Operating: 10 to 85% RH (max)

### Input Signal (VGA):

R.G.B. analog video, TTL H & V sync.

### Input Connector:

Display: 15-pin mini D-Shell



Offering OEM and custom solutions.  
Contact us for additional information.

[www.rackmountmart.com](http://www.rackmountmart.com)

Tel : 1-888-865-6888

Fax : 510-226-8968

Email : [sales@RackmountMart.com](mailto:sales@RackmountMart.com)