




Features

- 1U 21.5 or 23.8 inch widescreen LCD Console Drawer
- Screen Pivot with DVI & VGA Port
- 1920 x 1080 Ultra high resolution
- Support FHD with 1080p resolution.
- Front 1xUSB, Rear 2xUSB 2.0 Type A, Sharing USB peripheral Device for computer (ex, flash disk, hard driver, KB/Mouse)
- 104-key keyboard with touch pad mouse.
- USB 2.0 Keyboard & Mouse
- Self-locking and auto release rails for ultra convenience.
- Build in 2x 2 watts speakers

Options

- Composite Video input
- HDMI or Display Port input
- 3G / HD / SD –SDI Broadcast grade input
- 48V, 24V or 12V DC Power



Rear of LCD1U21-04 / LCD1U24-04

Part No.	LCD1U21-04	LCD1U24-04	
Direct no. of Computers	1		
KVM Connectors	DVI-D, VGA, USB		
LCD	Size	21.5 inch FULL HD display	23.8 inch FULL HD display
	Backlight	LED	
	Resolution	1920*1080 (support resolution up to 1920*1200)	1920*1080 (support resolution up to 1920*1200)
	Max.color	16.7M	
	Luminance	250 cd/m2	
	View Angel (H/V)	178 / 178	
	Contrast Ratio	3000 : 1	
USB HUB	1x Front , 2x Rear USB 2.0 Type A for peripheral USB devices		
Touch Screen	YES , for option (Driver needed)		
KB/Mouse Emulation	USB 2.0		
Audio	1 x 3.5 mm audio jack		
Rack Depth	600mm to 1200mm		
Power	100-240V AC 50/60Hz via IEC Type power cord		
Environment	Operation temp: 0 to 50°C		
	Storage temp: -20 to 60°C		
	Humidity: 10% - 90%, non-condensing		
	Shock: 10G acceleration (11ms duration) Vibration: 17 to 500Hz 1G PTP		
Physical Dimensions / Net Weights	448x44x698.5mm / 19 KGs	448x44x698.5mm / 20 KGs	