



Features

- 1U 23.8 inch widescreen LCD Console Drawer
- Screen Pivot with HDMI & Display Port
- 4K resolution 3840 x 2160
- Support 1920 x 1080 & 1920 x 1200 resolution
- Front 1xUSB, Rear 2xUSB 2.0 Type A, Sharing USB peripheral Device for computer (ex, flash disk, hard driver, KB/Mouse)
- 104-key keyboard with touch pad mouse.
- USB 2.0 Keyboard & Mouse
- Self-locking and auto release rails for ultra convenience.
- Build in 2x 2 watts speakers

Options

- 48V, 24V or 12V DC Power



Rear of LCD1U24-05

Part No.	LCD1U24-05	
Direct no. of Computers	1	
KVM Connectors	HDMI 2.0, Display port 1.4, USB	
LCD	Size	23.8 inch 4K display
	Backlight	LED
	Resolution	4K resolution 3840 x 2160
	Max.color	1.07 Billion colors
	Luminance	300 cd/m2
	View Angel (H/V)	178 / 178
	Contrast Ratio	1000 : 1
USB HUB	1x Front , 2x Rear USB 2.0 Type A for peripheral USB devices	
KB/Mouse Emulation	USB 2.0	
Rack Depth	600mm to 1200mm	
Power	100-240V AC 50/60Hz via IEC Type power cord	
Environment	Operation temp: 0 to 50°C	
	Storage temp: -20 to 60°C	
	Humidity: 10% - 90%, non-condensing	
	Shock: 10G acceleration ( 11ms duration)	
Physical Dimensions / Net Weights	Vibration: 17 to 500Hz 1G PTP	
	448x44x698.5mm / 20 KGs	