



Shown with optional mouse

FEATURES

- 88 Key compact keyboard with mouse storage and use area in 1U of vertical 19" rack space.
- Mounted with included smooth action ball bearing slides which lock in the extended position.
- Convenient area in front of keyboard for easy mouse use, mouse stores behind keyboard.
- Retainer and lock options to keep unit contained in the rack when not in use.
- Housed in rugged steel construction with a durable powder coat finish.
- Includes sturdy steel detachable cable management arm.
- Available with Cherry™ keyboard.



Offering OEM and custom solutions. Contact us for additional information.

KEYBOARD SPECIFICATIONS

Keys:	88 keys with Windows key
Rollover:	Alpha N-key rollover.
Auto repeat:	Yes.
Self Diagnostics:	At power on and system reset.
Reliability:	5M switch life cycles.
Pointing Device:	Optional Optical Mouse (M).

GENERAL SPECIFICATIONS

Dimensions:	19.0" (W) x 1.75" (H) x 20.00" (D) (22.75 D w/Cable Management)
Slides:	18" (20" extension) Adjustable for 22.75" to 31.5" mounting depth.
Weight:	15 lbs
Temperature:	Operating: 0°C to 50°C Storage: -20°C to 60°C
Humidity:	Operating: 10 to 85% RH Non Condensing (max)
Color:	Black

Specifications subject to change without notice.

Front Panel Option (Standard Color is Black)



Standard



-R : w/ Retainer Screws Option



-R-L : w/ Retainer Screw + Lock Option



-L : w/ Lock option