

LCDR5U10-03 10.4" LCD RACKMOUNT MONITOR WITH 24W SPEAKERS



- Dual 10.4" TFT LCD display (1024 x 768 resolution) in only 5U (8.75") of rack space.
- ARGB (Analog RGB) and DVI-D signal inputs (optional S-Video/Composite Video inputs).
- Housed in rugged steel construction with a black powder coat finish.
- Integrated 24 Watt stereo speaker with front panel controls.
- Optional Lexan. screen protection available (L).



Optional S-Video & Composite video input + ARGB



GENERAL SPECIFICATIONS

Dimensions:

19.0" (W) x 8.75" (H) x 5" (D)

Weight:

11 lbs

Power:

100 - 240 VAC, 50/60 Hz.
60 Watts max.

On-Screen Controls:

Brightness, Contrast, Horizontal & Vertical
Position, Auto Adjust, OSD H & V Position, Input Select
Color Temp., Reset.

Plug & Play:

DDC1 and DDC2B

Temperature:

Operating: 0°C to 50°C
Storage: -20°C to 60°C

Humidity:

Operating: 10 to 90% RH (max)

Input Signal (VGA):

R.G.B. analog video, TTL H & V sync.

Input Signal (Digital):

DVI-D (TDMS).

Input Connectors:

Analog: 15-pin mini D-Sub.
Digital: 24 pin DVI-D.

Colors Available:

Black.

DISPLAY SPECIFICATIONS

Display Type:

Active matrix TFT LCD

Viewable Size:

10.4" Diagonal.

Colors Displayed:

262k colors.

Contrast Ratio:

500:1

Brightness:

350 cd/m² typ.

Viewing Angle (CR>5):

Horizontal: 178°
Vertical: 178°

Response Time:

40ms Typ.

Resolution:

VGA up to 1024 x 768.

Horizontal Frequency:

30 to 81 KHz.

Vertical Frequency

55 to 75 Hz.

Screen Protection:

Lexan. optional.

SPEAKER SPECIFICATIONS

Front Panel Controls:

Power ON/OFF switch, Volume control,
Headphone jack, Power Indicator.

Audio Output:

24 Watts

Audio Input Connector:

3.5mm Stereo jack.



Supplied with VGA cables, AC/DC adapter and power cord.

Contact us about other options and our additional rack mount products.