

LCDR7U19-07 7U 19" 16:10 FORMAT MONITOR

(MADE IN U.S.A.)



- Mounts in 7U of 19" rack space.
- Wide format 16:10 aspect ratio.
- Fast 5 ms response time.
- 19" TFT LCD display with 1440 x 900 resolution.
- Analog (ARGB) and Digital (DVI-D) input connectors.
- Energy saving LED backlight.

GENERAL SPECIFICATIONS

- Dimensions:**
19.0" (W) x 12.25" (H) x 2.4" (D)
- Weight:**
8.5 lbs.
- Power:**
100 - 240 VAC, 50/60 Hz.
20 Watts.
- On-Screen Controls:**
Brightness, Contrast, Horizontal & Vertical Position, Auto Adjust, OSD H & V Position, Input Select Color Temp., Reset.
- Plug & Play:**
DDC2B
- Temperature:**
Operating: 10°C to 40°C
Storage: -20°C to 45°C
- Humidity:**
Operating: 10 to 80% RH (max)
- Input Signal (VGA):**
R.G.B. analog video, TTL H & V sync.
- Input Signal (Digital):**
DVI
- Input Connectors:**
Analog: 15-pin mini D-Sub.
Digital: 24 pin DVI-D.
- Colors Available:**
Black.

DISPLAY SPECIFICATIONS

- | | |
|---|---|
| Display Type:
Active matrix TFT LCD | Viewing Angle:
Horizontal: 170°
Vertical: 160° |
| Display area:
19" Wide. | Response Time:
5 ms. |
| Colors Displayed:
16.7 million colors. | Resolution:
Up to 1440 x 900. |
| Contrast Ratio:
1,000:1 (Mega Infinity Dynamic) | Aspect Ratio:
16:10. |
| Brightness:
250 cd/m ² typ. | Backlight type:
LED TN |
| EPEAT
Gold | |

Specifications subject to change without notice.

MODEL NUMBER

LCDR7U19-07

LCDR7U19-07-Lex with Lexan™ Screen Protection



Offering OEM and custom solutions.
Contact us for additional information.