



Current OSD control button



New Version OSD Control on Bottom of Frame

Mounts in 7U of rack space with mounting brackets to fit 19" rack width.  
 21.5" Wide format TFT LCD display with full HD 1920 x 1080 resolution.  
 Fast video response time provides sharp text and crisp motion.  
 16:9 aspect ratio provides a widescreen viewing area.

**GENERAL SPECIFICATIONS**

- Dimensions:**  
21.26"(W) x 12.22"(H) x 2.38"(D) front of mounting rails
- Weight:**  
12 lbs. including power adapter/cord
- Power:**  
100 240 VAC, 50/60 Hz.  
29 Watts max.
- Plug & Play:**  
DDC/C1
- Temperature:**  
Operating: 0°C to 40°C  
Storage: -20°C to 60°C
- Humidity:**  
Operating: 10 to 80% RH (max)  
Storage: 10 to 80% RH (max)
- Input Video Signals:**  
RGB Analog, HDMI
- Sync Type:**  
Separate sync
- Input Connectors:**  
15 pin Dsub, HDMI.
- Colors Available:**  
Black

**DISPLAY SPECIFICATIONS**

- Display Type:**  
IPS TFT LCD
  - Viewable Size:**  
21.5" wide format.
  - Colors Displayed:**  
16.7 million colors.
  - Contrast Ratio (Typ):**  
1000:1
  - Brightness:**  
250 cd/m<sup>2</sup> typ.
  - Viewing Angle (CR>10):**  
Horizontal: 178°  
Vertical: 178°
  - Response Time:**  
5 ms (G to G)
  - Native Resolution:**  
1920 x 1080  
(16:9 Format)
- Specifications subject to change without notice.

**MODEL NUMBER**

LCDR7U22-02

