



- 19" TFT LCD display (1280 x 1024 resolution) in only 8U (14.0") of rack space.
- Wide Horizontal and Vertical viewing angles offer viewing flexibility.
- Optional Lexan™ (L) or Touchscreen (T).
- VGA, HDMI, and DisplayPort Inputs.



**GENERAL SPECIFICATIONS**

- Dimensions:**  
19.0" (W) x 14.0" (H) x 1.7" (D)
- Weight:**  
11 lbs
- Power Supply:**  
110 - 240 VAC, 50/60 Hz  
60 Watts max
- On-Screen Controls:**  
Brightness, Contrast, Horizontal & Vertical Position, Auto Adjust, OSD H & V Position, Input Select  
Color Temp, Reset
- Temperature:**  
Operating: 0°C to 50°C  
Storage: -20°C to 60°C
- Humidity:**  
Operating: 5 to 90% RH (max)
- Input Signal (VGA):**  
R.G.B. analog video, TTL H & V sync
- Input Signal (Digital):**  
HDMI, DisplayPort
- Input Connectors:**  
Analog: 15-pin mini D-Sub  
Digital: HDMI, DisplayPort
- Colors Available:**  
Black

**DISPLAY SPECIFICATIONS**

- Display Type:**  
Active matrix TFT LCD
- Display area:**  
19" Diagonal
- Colors Displayed:**  
16.7 million colors
- Contrast Ratio:**  
2000:1 typ
- Brightness:**  
300 cd/m<sup>2</sup> typ
- Viewing Angle:**  
Horizontal: 178°  
Vertical: 178°

- Response Time:**  
18ms Typ
- Resolution:**  
VGA up to 1280 x 1024
- Horizontal Frequency:**  
31 to 80 KHz
- Vertical Frequency:**  
55 to 76 Hz
- Screen Protection:**  
Optional Lexan™ (L) or Touchscreen (T)

Specifications subject to change without notice.



Offering OEM and custom solutions.  
Contact us for additional information.