

RK1007 1U Rackmount Speakers



The RK1007 speaker system is a fully enclosed amplified stereo speaker system featuring front panel controls which include a Power ON/OFF and Volume Control Switch with Power Indicator. The front panel Headphone Jack disables the internal speakers when a headphone plug is inserted, directing audio output to the headphones. A front panel 3.5mm AUX input jack overrides the rear input source allowing connection of a second source. The unit is supplied with a detachable audio cable and an external 110 VAC 60Hz input power supply (optional 110/220 VAC 50/60 Hz input power supply).

GENERAL SPECIFICATIONS

Dimensions:

19.0" (W) x 1.75" (H) x 3.5" (D)

Weight:

3.7 lbs

Power Supply:

Standard - 110 VAC, 60 Hz.

Optional - 110/220 VAC, 50/60 Hz.

Colors Available:

Black.

Front Panel Controls:

Power ON/OFF switch, Volume Control, Headphone Jack, Power Indicator.

Audio Amplifier Output:

12 Watts.

Audio Input Connector:

1/8" (3.5mm) stereo jack.

Specifications subject to change without notice.



Rear View - 110VAC Power Supply



Rear View - 110/220VAC Power Supply



Offering OEM and custom solutions.
Contact us for additional information.