



Package Includes

- 12U Wallmount Rack Enclosure
- (36) M6 screws
- (36) M6 cage nuts
- (36) M6 washers
- (2) Keys
- Owner's Manual

Highlights

- 12U with adjustable front and rear vertical rackmount rails
- 33" depth accommodates most 1U servers and simplifies cable management
- Heavy duty construction supports the added leverage
- Hinged cabinet swings away from wall bracket for easy equipment access (swing direction is reversible)
- Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation
- PCI-Compliant: meets stringent physical security requirements

Features

- 12U wall-mounted enclosure
- Adjustable depths to 33" - accommodates most 1U servers
- Ventilated front door and side panels for increased airflow
- Hinged cabinet swings away from wall bracket for easy equipment and cable access
- Heavy duty construction to handle added leverage
- Locking, reversible front door
- Locking, removable side panels
- Top and bottom panel cable access openings

Description

This alternative 12U Extended-Depth Wall-Mount Rack Enclosure Cabinet is designed to integrate wall-mounting, easy equipment access, and cable management in IT network applications with limited floor space. Extended depth to 33" accommodates most 1U servers and provides extra clearance for cable management. It has a heavy-duty steel construction to handle the added leverage. Ventilated front door and side panels allow generous airflow to keep equipment operating safely. Adjustable rack rails with square mounting holes accommodate up to 12U of standard 19" rackmount equipment. A sturdy hinge between the cabinet and the wall-mount bracket allows the cabinet to swing away from the wall for easy access to equipment and cabling. Top and bottom panels include convenient cutouts for cable routing.

Specifications

PHYSICAL	
Installed whole system maximum rack depth (cm / in)	82.55 / 32.5
Installed whole system minimum rack depth (cm / in)	7.62 / 3
Installed whole system total rack space height (rack spaces)	12U
Unit weight (lbs / kg)	100 / 45.36
Unit Dimensions (cm / in)	EXTERNAL DIMENSIONS: 63.5 x 60 x 85.09 / 25 x 23.63 x 33.5
Color	Black
Weight Capacity - Stationary (lbs / kg)	250 / 113.4
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
SPECIAL FEATURES	
Grounding lug	Front and Back door frames
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, IP250 Protection Rating, RoHS