



### Specification

- \*PANEL-MOUNT TFT LCD monitor.(Analog VGA input.)
- \*Heavy-duty steel electroplated for chassis.
- \*VESA Ready
- \*15" TFT LCD Monitor
- \*Resolution 1024 x 768
- \*8 Languages on Screen Display Function (OSD)
- \*IP 65 at Aluminum front Panel
- \*USB 5 Wire resistive touch screen (RS232 Optional)

### Power Supply

- \*100V~220V AC Input, 12VDC Output (Standard)
- \*9V~33V DC Input, 24VDC Output (Optional)

### Power Consumption

- \*F€ Watts - AC power adapter
- \*48 Watts - DC power adapter (Optional)

**Color** Black

### Dimension

**W.**15.7 inch x **H.**11.8 inch x **D.**2.1 inch

**W.**402mm x **H.**302mm x **D.**53mm

Model#	Display Size	Active Area	Resolution	Brightness	Contrast Ratio	Response Time	Max Color	Viewing Angle (U/D/L/R)	Lamp MTBF
ID-3-15AN-TRB	15"	304.1x228.1	1024x768	250	500:1	20/5	16.7M	55/65/70/70	50,000
ID-3-15AN-TRS	15"	304.1x228.1	1024x768	250	500:1	20/5	16.7M	55/65/70/70	50,000
ID-3-15AN-TRB-DC24	15"	304.1x228.1	1024x768	250	500:1	20/5	16.7M	55/65/70/70	50,000
ID-3-15AN-TRS-DC24	15"	304.1x228.1	1024x768	250	500:1	20/5	16.7M	55/65/70/70	50,000