



Benefits

- ▶ 1U 17" / 19" LCD display drawer
- ▶ 1280 x 1024 native resolution / 16.7M colors
- ▶ DVI-D + VGA video input
- ▶ Short depth design of 480mm
- ▶ One Man installation design
- ▶ Enhanced aesthetics with molded front panel and two point lock

Options

- HDMI 1.4 + Audio input & output
- S-Video + Composite + Audio input & output
- 3G / HD / SD-SDI Broadcast-grade input
- DC power : 12V / 24V / 48V / 110V / 125V / 250V
- 17" Touchscreen :
Projected Capacitive 10-pt / Capacitive 1-pt / Resistive 1-pt
- 19" Touchscreen : Resistive 1-pt

Product Specifications

Video	
Video input	VGA + DVI-D single link

Video Option		
Digital	HDMI	HDMI 1.4 / HDCP 1.4
Analog	S-Video (4-pin)	NTSC & PAL
	Composite (BNC)	NTSC & PAL

LCD Panel	LCD1U17-013	LCD1U19-012
Panel size (diagonal)	17"	19"
Native resolution	1280 x 1024	1280 x 1024
Brightness (cd/m ²)	250	250
Contrast ratio (typ.)	1000 : 1	1000 : 1
Colors	16.7 M	16.7 M
Viewing angle (L/R/U/D)	85/85/80/80	85/85/80/80
Response time (ms)	5	5
Dot pitch (mm)	0.264	0.294
Display area (mm)	337.92H x 270.33V	376.32H x 270.33V
Surface treatment	Haze 25%, Hard-coating	
Surface hardness	3H	
Backlight type	LED	
MTBF (hrs)	30,000	

Audio Option		
Input	Connector	3.5mm stereo jack
	Impedance / Power level	30kΩ / 750mV
Output	Connector	3.5mm stereo jack
	Resistance / Power level	30kΩ / 2.8V
Speaker	Dual stereo	2W x 2

Power		
Input	Auto-sensing 100 to 240VAC, 50 / 60Hz	
Consumption	Screen on	Max. 22W
	Power saving mode	Max. 2W
	Power button off	Max. 1W

Environment	
Operating temp.	0 to 55°C degree
Storage temp.	-20 to 60°C degree
Operating humidity	10~90%, non-condensing
Storage humidity	5 ~90%, non-condensing
Operating altitude	16,000 ft
Non-operating altitude	40,000 ft
Shock	10G acceleration (11ms duration)
Vibration	10~300Hz 0.5G RMS random vibration

Compliance	
EMC	FCC & CE
Safety	CE / LVD & UKCA
Environment	REACH & RoHS3 / WEEE

Mounting Distance	
Display drawer	490 ~ 720 mm 19.3 ~ 28.3 inch

Physical		LCD1U17-013	LCD1U19-012
Dimensions (W x D x H)	Product	442 x 480 x 44 mm 17.4 x 18.9 x 1.73 inch	442 x 480 x 44 mm 17.4 x 18.9 x 1.73 inch
	Weight	10.5 kg / 23.1 lb	12.5 kg / 27.5 lb

* All dimensions stated are subject to change if options are selected / integrated to base model part codes

Diagrams (mm)

