

LCD1U17-014 / LCD1U19-013 1U 17", 19" Rackmount SUN LCD Drawer



Drawer Features & Display Benefits

- ▶ 1U 17" or 19" LCD drawer
- ▶ Direct Support for SUN Micro 1152 x 900 native resolution
- ▶ Short depth design of 500mm (19.7")
- ▶ Depth will suit a 600mm rack application
- ▶ Sliding LCD allowing LCD to remain open when the rack door is closed
- ▶ Installation slides for easy, quick installation
- ▶ Enhanced aesthetics with molded front panel and two point lock

Options

- DC power : 12V / 24V / 48V / 110 ~ 125V



Basic I/O : VGA and DVI-D

** For DC power option, casing depth will be extended from 500mm (19.7") to 570mm (22.4")

Specifications

• LCD Panel

Manufacturer :	AUO	AUO
Size (diagonal) :	17" TFT	19" TFT
Direct resolution :	1152 x 900	1152 x 900
Native resolution :	1280 x 1024	1280 x 1024
Brightness (cd/m ²) :	250	250
Backlight :	CCFL	LED
Colors :	16.7 M	16.7 M
Contrast ratio (typ) :	1000 : 1	1000 : 1
Viewing angle (H/V) :	160° x 160°	170° x 160°
Active area (mm) :	338 x 270	376 x 301
MTBF (hrs) :	50,000	30,000
Signal input :	VGA or DVI-D	VGA or DVI-D

• **Power Input :** Auto-sensing 100 to 240VAC, 50 / 60Hz

• Power Consumption

Screen on :	Max. 25W
Power saving mode :	Max. 4W
Power button on :	Max. 1W

• Environmental

Operating temperature :	0 to 55°C degree
Storage temperature :	-20 to 60°C degree
Operating humidity :	20~90%, non-condensing
Storage humidity :	5 ~90%, non-condensing
Operating altitude :	16,000 ft
Non-operating altitude :	40,000 ft
Shock :	10G acceleration (11ms duration)
Vibration :	5~500Hz 1G RMS random vibration

• Casing Color :

Black (RAL 9005)

• Regulatory

Safety :	FCC & CE certified
Environmental :	RoHS2 & REACH compliant

• Weight

	Net
LCD1U17-014 :	10.5 kgs / 23.1 lbs
LCD1U19-013 :	12.5 kgs / 27.5 lbs

• Dimensions

Product :	441.6 x 500 x 44 mm / 17.4 x 19.7 x 1.73 inch
-----------	---

Diagrams (mm)

