



Drawer Features & Display Benefits

- ▶ 1U design with 17.3" TFT LCD
- ▶ 16:9 - 1080p LCD monitor
- ▶ Built-in amplified speakers
- ▶ USB or PS2 connector
- ▶ Quality keyboard with Touchpad
- ▶ Work with standard PCI-E video
- ▶ VGA or DVI-D signal

Specifications

• LCD Panel

Size (diagonal) :	17.3" (16:9) TFT
Max resolution :	1920 x 1080
Brightness (cd/m2) :	300
Backlight :	LED
Colors :	262K
Contrast ratio (typ) :	650 : 1
Signal input :	VGA or DVI-D
Response :	8ms

• Casing Color :

Black

• Weight

Net :	20 lbs
-------	--------

• Environmental

Operating :	0 to 50°C Degree
Storage :	-20 to 60°C Degree
Relative humidity :	10~90%, non-condensing
Oper. Altitude :	0 ~ 3,000m or 10,000ft

• Power

Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 60 Watt

• Dimensions

Product :	19 x 14.5~24 x 1.75 inch
-----------	--------------------------

