



6mm aluminum front bezel with optional

NEMA 4 / IP65 front protection




Display Benefits

- ▶ 17" widescreen LCD with **Full HD** 1080p resolution
- ▶ Green LED-backlit panel technology
- ▶ Rugged construction against external impact
- ▶ Protective 3mm glass


Options

- 3G / HD / SD-SDI Broadcast-grade input (w/ speaker)
- **MC** Multi-display control solution
- 17" Touchscreen : Resistive
- NEMA4 / IP65 front protective glass
- HDMI, S-Video + Composite (BNC) or Audio input
- MIL-type or lockable connector
- 48V, 24V or 12VDC power
- TV - Analog

Basic I/O



Ver. 3.0 upgrade I/O with advanced features



Specifications

• **LCD Panel**

- Size (diagonal) : 17.3" Widescreen TFT
- Max resolution : 1920 x 1080
- Brightness (cd/m2) : 400
- Backlight : LED
- Colors : 16.7 M, 8-bit
- Contrast ratio (typ) : 600 : 1
- Viewing angle (H/V) : 160° x 140°
- Active area (mm) : 382 x 215
- MTBF (hrs) : 50,000
- Signal input : DVI-D / VGA

• **Weight**

Net : 5.2 kgs (11.4 lbs)

• **Mounting :**

Panel mount / VESA mount

• **Environmental**

- Operating : 0 to 50°C Degree
- Storage : -5 to 60°C Degree
- Relative humidity : 5~90%, non-condensing
- Shock : 10G acceleration (11 ms duration)
- Vibration : 5~500Hz 1G RMS random vibration

• **Casing Color :**

Black front panel (RAL 9005)
Dark grey rear case (RAL 7037)

• **Regulatory :**

FCC, CE, RoHS

• **Power**

- Input : Auto-sensing 100 to 240VAC, 50 / 60Hz
- Consumption : Max. 48 Watt, Standby 5 Watt

• **Dimensions**

Product : 468.5 x 57.1 x 331 mm / 18.4 x 2.2 x 13 inch

Diagrams (mm)

Front View

Side View

Rear View

