

Universal open frame mounting




Display Benefits

- ▶ 17" widescreen LCD with **Full HD** 1080p resolution
- ▶ Green LED-backlit panel technology
- ▶ Rugged construction against external impact


Options

- 3G / HD / SD-SDI Broadcast-grade input ( w/ speaker )
- **MC** Multi-display control solution
- 17" Touchscreen : Resistive
- HDMI, S-Video + Composite ( BNC ) or Audio input
- MIL-type or lockable connector
- 48V, 24V or 12VDC power
- TV - Analog

Basic I/O



Ver 3.0 upgrade I/O with advanced features



Specifications

• LCD Panel

- Size (diagonal) : 17.3" Widescreen TFT
- Max resolution : 1920 x 1080
- Brightness (cd/m2) : 400
- Backlight : LED
- Colors : 16.7 M, 8-bit
- Contrast ratio (typ) : 600 : 1
- Viewing angle (H/V) : 160° x 140°
- Active area (mm) : 382 x 215
- MTBF (hrs) : 50,000
- Signal input : DVI-D / VGA

• Weight

- Net : 3.4 kgs ( 7.5 lbs )

• Mounting :

- Universal mount / VESA mount

• Environmental

- Operating : 0 to 50°C Degree
- Storage : -5 to 60°C Degree
- Relative humidity : 5~90%, non-condensing
- Shock : 10G acceleration ( 11 ms duration )
- Vibration : 5~500Hz 1G RMS random vibration

• Casing Color :

- Dark grey ( RAL 7037 )

• Regulatory :

- FCC, CE, RoHS

• Power

- Input : Auto-sensing 100 to 240VAC, 50 / 60Hz
- Consumption : Max. 48 Watt, Standby 5 Watt

• Dimensions

- Product : 465.5 x 50.6 x 328 mm / 18.3 x 2 x 12.9 inch

Diagrams ( mm )

Front View

Side View

Rear View

