



(USB Port for single-port model only)

**Features**


- KVM switch supports combo interface, VGA-USB & VGA-PS2
- Short depth design suit for mobile rack and limited space.
- Durable 88-key keyboard and touch pad.
- Quick and simple installation.
- Self-locking and auto release rails for ultra convenience.
- Port selection via push buttons or On-Screen-Display (OSD).
- Dedicated daisy chain port to expand up to 240 servers.

**Options**


- 8-port or 16-port KVM switch (Front & Rear USB will be removed when adding KVM switch)
- Composite Video input
- HDMI or Display Port input
- 3G / HD / SD SDI Broadcast grade input
- 48V, 24V or 12V DC Power



Rear of LCD1U15-17-n



Rear of LCD1U15-17-8KVM



Rear of LCD1U15-17-16KVM

Part No.	LCD1U15-17	LCD1U15-17-8KVM	LCD1U15-17-16KVM
Direct no. of Computers	1	8	16
Maximum no. of Computers	1	232(Daisy Chain)	240(Daisy chain)
LCD	Size	17.3"	
	Backlight	LED	
	Resolution	1920*1080 Full HD ( support resolution up to 1920x1200 )	
	Max.color	262K	
	Luminance	300cd/m2	
	View Angel (H/V)	140 / 120	
	Contrast Ratio	650 : 1	
Port Selection	N/A	Push Button,OSD or Hotkey	
USB Local console / Expansion Slot	N/A		
KB/Mouse Emulation	USB & PS2		
Rack Depth	380mm to 620mm ( rack cabinet front rails to rear rails )		
Power	100-240V AC 50/60Hz via IEC Type power cord		
Environment	Operation temp: 0 to 50°C		
	Storage temp: -20 to 60°C		
	Humidity: 10% - 90%, non-condensing		
	Shock: 10G acceleration ( 11ms duration) Vibration: 17 to 500Hz 1G PTP		
Physical Dimensions / Net Weights	443x42x457.2mm (WxHxD) /14KG		