

# RM3017 19" 3U Rackmount Chassis



## Specifications

- EIA RS-310C 19" Rackmount Standard
- Construction: Heavy Duty Cold Rolled Electroplated Steel
- Color: Black (Standard)
- System Boards: Pentium 4, Athlon 64, Dual Xeon, Dual Opteron
- Support ATX M/B (Max. to 12" x 9.6")
- Drive Capacity: 2x 5.25" CD-ROM & 1x 3.5"FDD & 3x 3.5"HDD
- Power Supply (Optional): 2U Single up to 600W or 2U Redundant up to 500W ATX P/S Max. Depth 300mm
- Cooling: 2x (60 mm = 23.5CFM ea.) & 2x (40 mm = 7CFM ea.) Fans
- Front Door: Single Door With Thumb Twist Keylock
- Connector Port (Front): 2x USB Ports
- LCD Size: 7" TFT with 800\*480 Resolution With Touch Screen
- Display Colors: 262,144 colors
- Indicators: LEDs for Power ON/OFF, HDD Activity, LAN
- Switch: Power ON/OFF, System Reset
- Dimensions (W x H x D): 483 x 133 x 524mm (19" x 5.2" x 20.6")
- Cuft: 4.2
- Humidity: 5% - 95% Non-condensing

## Dimension

