


Cordset : 3 meter UL 10AWG cable with 30 Amp NEMA L6-30P plug
Circuit Breaker : 2 x 15A Circuit Breaker
Input Rating : 30A / 200~240Vac

For 30A Rating PDU, the models which have 20 socket outlets,
< CIRCUIT A > Socket #1-10 C13 socket outlets can only output 12A maximum.
< CIRCUIT B > Socket #11-20 C13 socket outlets can only output 12A maximum.

Model : V20C13-20A-WSi/CR_L620/3B-1



Cordset : 3 meter UL 12AWG cable with 20 Amp NEMA L6-20P plug
Circuit Breaker : 1 x 20A Circuit Breaker
Input Rating : 20A / 200~240Vac

For 20A Rating PDU, the models which have 20 socket outlets,
Socket #1-20 C13 socket outlets can only output 16A maximum.

UNIT : inch

Common Specification :

Description : 20 outlets IEC320 C13
Receptacles : 20 outlets IEC320 C13 10A Rated
Meter : RMS digital ammeter measuring input load current

PDU Dimension : 2.76 (W) x 2.56 (D) x 47.24 (H) in.
Packing :

Net Weight :
Gross Weight :

WARNING : The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.

Copyright 2012 Synergy Global Technology Inc. All rights reserved.