



32A model :	Fuse	MCB
VP12C13-32A-CR_EN/2B-1	-	6

- Input Rating : 32A, 400V
- Inlet : 32A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
- Protection : 16A single pole hydraulic MCB x 6
- Bank Details :
  - PH-1 < Bank 1 > Output 16A max. C 13 # 1 - 2
  - < Bank 2 > Output 16A max. C 13 # 3 - 4
  - PH-2 < Bank 3 > Output 16A max. C 13 # 1 - 2
  - < Bank 4 > Output 16A max. C 13 # 3 - 4
  - PH-3 < Bank 5 > Output 16A max. C 13 # 1 - 2
  - < Bank 6 > Output 16A max. C 13 # 3 - 4

**Three phase basic PDU**

Outlet : 10A Rated IEC320 C13 x 12



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.

Copyright 2015 Synergy Global Technology Inc. All rights reserved.

EMC Compliance : FCC & CE certified  
Safety Compliance : CE / LVD certified  
Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C  
Storage Temperature : -25 to 65 °C  
Operating Altitude : 0 to 2,000 m  
Storage Altitude : 0 to 15,000 m  
Humidity : 8 to 95% RH, non-condensing

Dimension : 70 (W) x 83 (D) x 1200 (H) mm  
Material : Extrusion  
Color : Black