


Date : 1 Dec 15  
Version : V3

# PDU specification drawing

## 3-Phase 400V 16A basic PDU : SCH x 24



16A model :	Fuse	MCB
VP24SCH-16A-CR_EN/2B-1	-	<b>3</b>

Input Rating : 16A, 400V  
 Inlet : 16A IEC60309 3P+N+E 6hr Red plug  
 Cordset : 5-wire 2 meter 1.5mm sq. H07RN-F cordset  
 Protection : 16A single pole hydraulic MCB x 3  
 Phase Details : < **PH-1** > Output 16A max. S C H # 1 - 8  
                   < **PH-2** > Output 16A max. S C H # 1 - 8  
                   < **PH-3** > Output 16A max. S C H # 1 - 8

**Three phase basic PDU**  
 Outlet : 16A Rated Schuko x 24



The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.  
 Copyright 2015 Synergy Global Technology Inc. All rights reserved.

EMC Compliance : FCC & CE certified  
 Safety Compliance : CE / LVD certified  
 Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

Dimension : 70 (W) x 83 (D) x 1650 (H) mm  
 Material : Extrusion  
 Color : Black