

LCDR8U20-08 20" WIDE FORMAT LCD RACK MOUNT MONITOR

(Made in U.S.A.)



- Mounts in 8U of vertical rack space within 19" rack width.
- 20" Wide format TFT LCD display with 1600 x 900 resolution.
- 16:9 aspect ratio features a widescreen viewing area.
- Steel front panel construction with a durable paint finish.
- LED back light for energy savings.

GENERAL SPECIFICATIONS

Dimensions:

19.0" (W) x 14.0" (H)
D = 2.3" (1.7" in front of rack mounting rails)

Power:

100 - 240 VAC, 50/60 Hz.
25 Watts max.

Plug & Play:

DDC2B

Temperature:

Operating: 10°C to 40°C
Storage: -20°C to 45°C

Humidity:

Operating: 10 to 80% RH (max)

Input Video Signals:

R.G.B. analog, DVI (with HDCP)

Sync Type:

Separate H/V, Composite H/V, SOG.

Input Connectors:

15 pin D-sub, DVI-D.

Compatibility:

PC/Windows, Macintosh.

Colors Available:

Black.

DISPLAY SPECIFICATIONS

Display Type:

a-si TFT/TN

Viewable Size:

20" wide format.

Colors Displayed:

16.7 million colors.

Contrast Ratio:

DC 10,000,000:1 (1000:1)

Brightness:

250 cd/m² typ.

Viewing Angle (CR>5):

Horizontal: 170°
Vertical: 160°

Response Time:

5 ms (G to G)

Native Resolution:

1600 x 900.

Specifications subject to change without notice.

MODEL NUMBER

LCDR8U20-08

Contact us about other options and our additional rack mount products.



LCDR8U20-08 shown mounted in a standard 19" equipment rack.