

# RK1004 1U RACK MOUNT SPEAKER SYSTEM



Featuring a rugged fully enclosed amplified stereo speaker system with front panel controls which include a Power ON/OFF Switch with Indicator and a separate Volume Control. A Headphone Jack located on the front panel disables the internal speakers when a headphone plug is inserted, directing audio output to the headphones. The unit is supplied with a detachable audio cable and an external 110 VAC 60 Hz input power supply (optional 110/220 VAC 50/60 Hz input power supply).

## GENERAL SPECIFICATIONS

### Dimensions:

19.0" (W) x 1.75" (H) x 3.5" (D)

### Weight:

3.7 lbs

### Power Supply:

Standard - 110 VAC, 60 Hz.

Optional - 110/220 VAC, 50/60 Hz.

### Colors Available:

Black.

### Front Panel Controls:

Power ON/OFF switch, Volume Control, Headphone Jack, Power Indicator.

### Audio Amplifier Output:

24 Watts.

### Audio Input Connector:

1/8" (3.5mm) stereo jack.

Specifications subject to change without notice.

*Contact us about other options and our additional rack mount products.*