

PDU Inquiry Form








PDU Series:
 W (Monitored PDU with circuit level measurement)
 Wi (Monitored PDU with outlet level measurement)
 MD (Local metered PDU)
 WS (Switched PDU with circuit level measurement)
 WSi (Switched PDU with outlet level measurement)

Form factor:
 Vertical
 Horizontal

PDU qty:

IP dongle qty:

- Required for **W / WS / Wi / WSi** PDU series
 - 1 x IP dongle supports daisy chain up to 16 PDUs

PDU Configuration:	Voltage	No of outlet	Circuit Breaker or Fuse	Current	Input Plug Type	Length of Power cord	Power Entry	C13 / C19 Colored Outlet	Colored Casing
<input type="checkbox"/> 110V NEMA 5-20R	<input type="checkbox"/> 32 <input type="checkbox"/> 28 <input type="checkbox"/> 24 <input type="checkbox"/> 20 <input type="checkbox"/> 16 <input type="checkbox"/> 12 <input type="checkbox"/> 10 <input type="checkbox"/> 8 <input type="checkbox"/> 6 <input type="checkbox"/> 4 Others _____	 NEMA 5-20R	<input type="checkbox"/> Circuit Breaker or <input type="checkbox"/> Resettable Fuse	<input type="checkbox"/> 20A	<input type="checkbox"/> 5-20P or <input type="checkbox"/> L5-20P	<input type="checkbox"/> Standard: 3M/9.8ft or Others _____	<input type="checkbox"/> Single Feed or <input type="checkbox"/> Top or <input type="checkbox"/> Bottom	<input type="checkbox"/> Black (Standard) or <input type="checkbox"/> Red or <input type="checkbox"/> Blue or Others _____	
				<input type="checkbox"/> 30A	<input type="checkbox"/> 5-30P or <input type="checkbox"/> L5-30P		<input type="checkbox"/> Dual Feed or <input type="checkbox"/> Top or <input type="checkbox"/> Bottom		
<input type="checkbox"/> 208V 1PH	<input type="checkbox"/> C13 (Standard) <input type="checkbox"/> C13 (Lockable) <input type="checkbox"/> C13 (Individually Fused) <hr/> <input type="checkbox"/> C19 (Standard) <input type="checkbox"/> C19 (Lockable) <input type="checkbox"/> C19 (Individually Fused)	 IEC320 C13  IEC320 C19	<input type="checkbox"/> Circuit Breaker or <input type="checkbox"/> Resettable Fuse	<input type="checkbox"/> 20A	<input type="checkbox"/> L6-20P or <input type="checkbox"/> L6-30P	<input type="checkbox"/> Standard: 3M/9.8ft or Others _____	<input type="checkbox"/> Single Feed or <input type="checkbox"/> Top or <input type="checkbox"/> Bottom	<input type="checkbox"/> Black (Standard) or <input type="checkbox"/> Red or <input type="checkbox"/> Blue or Others _____	
				<input type="checkbox"/> 30A	<input type="checkbox"/> L6-30P		<input type="checkbox"/> Dual Feed or <input type="checkbox"/> Top or <input type="checkbox"/> Bottom		
<input type="checkbox"/> 208V 3PH	<input type="checkbox"/> C13 (Standard) <input type="checkbox"/> C13 (Lockabked) <input type="checkbox"/> C13 (Individually Fused) <hr/> <input type="checkbox"/> C19 (Standard) <input type="checkbox"/> C19 (Lockable) <input type="checkbox"/> C19 (Individually Fused)	 IEC320 C13  IEC320 C19	<input type="checkbox"/> Circuit Breaker or <input type="checkbox"/> Resettable Fuse	<input type="checkbox"/> 20A	<input type="checkbox"/> L15-20P or <input type="checkbox"/> L21-20P	<input type="checkbox"/> Standard: 2M/7.8ft or Others _____	<input type="checkbox"/> Single Feed or <input type="checkbox"/> Top or <input type="checkbox"/> Bottom	<input type="checkbox"/> Black (Standard) or <input type="checkbox"/> Red or <input type="checkbox"/> Blue or Others _____	
				<input type="checkbox"/> 30A	<input type="checkbox"/> L15-30P or <input type="checkbox"/> L21-30P		<input type="checkbox"/> Dual Feed or <input type="checkbox"/> Top or <input type="checkbox"/> Bottom		
<input type="checkbox"/> 50A	<input type="checkbox"/> CS8365C	 50 Amp Hubbell CS8365C	<input type="checkbox"/> 60A	<input type="checkbox"/> IEC 60309 60A 3P+E 9h Blue Plug (IP67)	 IEC 60309 60A 3P+E 9h Blue PLUG (IP67)				