


4K UHD LED

4K ULTRA Hi-DEFINITION

PROFESSIONAL




OVERVIEW

Our newly developed 42.51 inch professional monitor features a 4K 3840 x 2160 resolution. These monitors accept 4K signals at the multiple and various interfaces: DisplayPort 60p, HDMI 60p. There is also optional 3G or 6G-SDI signal support.

FEATURES

- » High Resolution(3840x2160) Panel with LED Backlight
- » Anti-Reflection Front Coating
- » Full 60fps Frame Rate
- » Multi-Input Interface: Display Port, HDMI, DVI, VGA, SDI(Optional)
- » Dynamic Contrast: ON / OFF
- » Wide Viewing Angle
- » 3D De-interlace
- » Rotation Screen/OSD menu (90/180/270)
- » Industrial Grade Metal Cabinet




24/7365
Built to run 24 x 7 x 365
Continuously

SPECIFICATIONS

Display	
Screen Size	42.51 Inch
Max. Resolution	3840 x 2160
Pixel Pitch	0.2451 x 0.2451mm
Brightness	500cd/m ²
Contrast Ratio	1000 : 1
Aspect Ratio	16 : 9
Viewing Angle (H/V)	178° / 178°
Display Color	1.07 Billion
Response Time	< 8ms
Video System	NTSC / PAL
Interface	
Display Port In/ Out	1 / 1
HDMI Input	3
DVI In	1
VGA In	1
3G-SDI In / Out	Option
Audio Out (3.5 Ø stereo)	1
Transmitter	
Remote Control	Yes
Audio	
Built-in Speakers	Yes (5W x 2)
Features	
Multi Display Function	PIP/PBP/TRI/QUAD
Deinterlacing	Yes
Noise Reduction Control (NR)	Yes
Aspect Ratio	Yes
Dynamic Contrast	Yes (On / Off)
Gamma Selection	Yes (On / Off)
General	
Outline Dimension (W x H x D)	967.2 x 613.3 x 240mm (38.08"x24.15"x 9.45")
Net Weight	20 kg (44.09 lbs)
Material / Color	Metal / Black
Desk Top Stand	Foot Type
Part / Labor	3 Years Parts & Labor
Consumption	< 70W
Electrical Ratings	AC100 ~ 240V(50/60Hz)
Operating Temperature	0° ~ 50° C / 32° ~ 122° F
Storage Temperature	-20° ~ 60° C / -4° ~ 140° F
Mounts	
VESA™ Mount Size	300 x 300mm
Wall	WB-4663, WB-S3763, WB-2642
Ceiling	CMH-01

*Design and specifications are subject to change without notice


INTERFACE



<BOTTOM>

- ① **VGA** : VGA signal Input
- ② **DVI** : DVI signal Input
- ③ **HDMI1~3** : HDMI1~3 Input
- ④ **DP** : DP Input
- ⑤ **USB** : FW Update Input
- ⑥ **DP** : DP Output
- ⑦ **Audio** : Audio Line Output
- ⑧ **AC Power** : AC Power Inlet

DIMENSIONS



OPTIONAL MOUNTS



PRODUCT VIEW

