



Screen	4 x 4.41" LCD
Chassis	2RU
Resolution	1920 x 1080
Aspect Ratio	16: 9
Viewing Angle	(H) +85/-85° ; (V) +85/-85°
Brightness	400 cd/m <sup>2</sup>
Contrast Ratio	1500 : 1
Video Input	4 x 3G/HD/SD-SDI 4 x HDMI
Video Loop out	4 x 3G/HD/SD-SDI 4 x HDMI
Input Formats	<p><b>SDI:</b> SD: 480i 59.94 / 576i 50 HD: 720p 23.98/24/25/29.97/30/50/59.94/60 1080i 50/59.94/60 1080p 23.98/23.98sf/24/24sf/25/25sf/29.97/29.97sf/30/30sf</p> <p><b>3G-level A:</b> 720p 23.98/24/25/29.97/30/50/59.94/60 1080p 23.98/23.98sf/24/24sf/25/25sf/29.97/29.97sf/30/30sf/50/59.94/60 1080i 50/59.94/60</p> <p><b>HDMI:</b> 480i59.94 / 480p59.94 / 576i50 / 576p50 720p50/59.94/60 1080p23.98/24/25/29.97/30 1080i50/59.94/60 1080p50/59.94/60 3840x2160 p23/24/25/29/30/50/59/60 4096x2160 p23/24/25/29/30/50/59/60 640x480 60 / 720x480 60 / 720x576 60 / 800x600 60 1024x768 60 / 1280x768 60</p>
Audio In	-Embedded Audio from SDI and HDMI
Audio Out	- SDI and HDMI embedded audio from 3.5mm headphone jack -Embedded audio from SDI and HDMI loop out
Control	-On-screen tally from 15-pin D-Sub port
Power	DC input support 10 ~ 24V (typical 12V), 24W
Storage Temperature	(-20)°C ~ (+ 60)°C
Operating Temperature	(0)°C ~ (+ 50)°C
Dimensions	19" x 3.5" x 1.5" (482.7mm x 88mm x 38mm)
Weight	3.50 lbs (1.6kg)
Features	Safety marker, aspect marker, center marker, marker color, check field, peaking color, peaking level, audio meter, image flip, image freeze, aspect ratio, scan modes, 2 user defined function buttons