



Key Benefits

- ▶ Screen Size:4.5 inches
- ▶ Resolution:1280 x 720
- ▶ Aspect Ratio:16:9
- ▶ Quad displays in a compact 2U height - only 1.4" deep
- ▶ Brightness:500 nits
- ▶ Inputs:HDMI, 3GSDI
- ▶ SDI and CVBS have loop through



Number of Panels	4
Panel Size	4.5" Screen, rack mount, 2RU (3.5") High
Resolution (Pixels)	1280 x 720
Aspect Ratio	16:9
Backlight	Adjustable LED Backlight
Viewing Angle	80°/80°(L/R), 80°/80°(U/D) - excellent off-axis color and brightness
Brightness (in cd/m2)	500
Contrast Ratio	1000:1
Video Inputs	3G-SDI x 4, HDMI x 4, CVBS x 4
Video Loopout	3G-SDI x 4, CVBS x 4
Audio Inputs	Supports HDMI and SDI embedded audio, RCA jacks accept analog audio for CVBS input
Audio Outputs	Front panel 3.5mm stereo headphone jack
Tally Connector	15-pin D-Sub port for Tally control
Power	12 Volts DC @ 2 Amps nominal (10V - 24V range) via 5.5mm x 2.1mm locking coaxial jack
Compliance	FCC-Class A, CE
Dimensions	19.0"W x 3.3"H x 1.4"D (482.5mm W x 84mm H x 35.8mm D)
Weight	3.53lbs, 1.6kg