



- 17.3" Full HD (1920 x 1080 resolution ) TFT LCD display
- Mounts flush in 6U (10.5") of vertical 19" rack space
- Steel front panel construction with a durable powder coat finish
- 600:1 Static contrast ratio provides superior detail
- HDMI, DP, and VGA inputs

### GENERAL SPECIFICATIONS

#### Dimensions:

19.0" (W) x 10.5" (H) x 1.6" (D)

#### Weight:

7.5 lbs

#### Power:

110 - 240 VAC, 50/60 Hz  
17 Watts typical

#### Temperature:

Operating: 0°C to 70°C  
Storage: -20°C to 70°C

#### Humidity:

Operating: 5 to 95% RH (max)

#### Input Signal (VGA):

RGB analog video

#### Input Signal (Digital):

HDMI, DisplayPort (DP)

#### Input Connectors:

Analog: 15-pin mini D-Sub  
Digital: HDMI, DP

#### Colors Available:

Black

### DISPLAY SPECIFICATIONS

#### Display Type:

TFT active matrix LCD

#### Viewable Size:

17.0" diagonal

#### Colors Displayed:

16.7 million colors

#### Contrast Ratio :

600:1

#### Brightness:

400 cd/m<sup>2</sup> typ

#### Viewing Angles:

160°/140° H/V

#### Response Time:

37/3 ms Typ (Tr/Td)

#### Optimum Resolution

1920 x 1080

#### Light Source:

Long Life (50,000 hrs typ)

#### Panel Surface:

Anti-glare

Specifications subject to change without notice.

Offering OEM and custom solutions.  
Contact us for additional information.

