

ID-40Pw-LED 40" High Resolution Widescreen LCD Panel w/ LED-backlit Display



Universal open frame mounting

FC CE

Display Benefits

- ▶ 40" widescreen LCD with **Full HD** 1080p resolution
- ▶ Green LED-backlit panel technology
- ▶ Rugged construction against external impact
- ▶ Standard with HDMI, DVI-D, VGA, S-Video, RCA, Audio & remote controller

Options

- 3G / HD / SD-**SDI** Broadcast-grade input
- **MC** Multi-display control solution
- MIL-type or lockable connector
- TV - PAL or NTSC



Standard I/O : HDMI, DVI-D, Audio, S-Video, RCA, VGA

Options I/O : TV
SDI or MC (either one)

Specifications

• LCD Panel

Manufacturer :	
Size (diagonal) :	40" TFT
Max resolution :	1920 x 1080
Brightness (cd/m ²) :	400
Backlight :	LED
Colors :	16.7 M
Contrast ratio (typ) :	4000 : 1
Viewing angle (H/V) :	178° x 178°
Active area (mm) :	886 x 498
MTBF (hrs) :	30,000
Signal input :	HDMI / DVI-D / VGA / S-Video / RCA

• Weight

Net : 45 kgs (99 lbs)

• Mounting :

Universal mount / VESA mount

• Environmental

Operating :	0 to 50°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5~90%, non-condensing
Shock :	10G acceleration (11 ms duration)
Vibration :	5~500Hz 1G RMS random vibration

• Casing Color :

Dark grey (RAL 7037)

• Regulatory :

FCC, CE

• Power

Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 200 Watt, Standby 20 Watt

• Dimensions

Product : 986 x 71 x 599 mm / 38.8 x 2.8 x 23.6 inch

Diagrams (mm)

