



Triple Full HD LCD Monitors

The LCD monitors are built inside a slim and rugged aluminum housing for durability. The display mechanism is hinged so it can be tilted to the most comfortable viewing position. LCD folds flat on top of keyboard when recessed into the drawer. An auto shut-off switch will turn-off the power to the LCD monitor when the LCD is in recess position.

Keyboard and Mouse

LCD2U17-3H-01 has built in keyboard and touch pad in bottom drawer below the monitors that operates independently.

Power Supply and Connectors

The LCD monitor is powered by a 60W 100-240V full-range power supply positioned at the back of the drawer with a rocker on-off switch. The keyboard, mouse and video connectors are also positioned at the back of the drawer for easy access.

Security

A key locking mechanism locks the drawer when in the full recess position to prevent unauthorized access.

General Specifications

- LCD size: 17.3" x 3
- Resolution: 5760x1080
- Color: 262K
- Brightness: 300 cd/m2
- Contrast: 400:1
- Response: 8ms
- Video Input: Display Port, mini DP, HDMI, DVI
- Interface: USB
- Mouse type: Touch pad
- Sound: Amplified stereo speakers

Dimension and Weight

- Height: 3.5" (2U)
- Width: 19"
- Depth: 22.3" ~ 34" adjustable
- Weight: 39LBS

Operating Environment

- Temperature: 0 to 50°C
- Humidity: Meth 5%-95% RH, non-condensing
- Altitude: 15,000 ft.
- Shock: 15g, 11ms
- Vibration: 20-60Hz, 0.075mm
- Drop: 3 feet height free drop

Storage Environment

- Temperature: -20 to 50°C
- Humidity: Meth 5%-95% RH, non-condensing
- Altitude: 40,000 ft.
- Shock: 50g, 11ms
- Vibration: 10-50Hz, 0.15mm
- Drop: 3 feet height free drop
- EMI & Safety: FCC Class B, CE

