

## 2U Rackmount Speaker RK1001

**Synergy Global Technology Inc / RackmountMart.com**

2U (3.5") high 4 Watt amplified stereo speakers. Headphone Jack, Power Indicator, ON/OFF Switch and Volume Control mounted behind front panel door. Complete with 110 VAC power adapter and input cable.

### FEATURES

- \* Amplified speakers.
- \* 4 Watts.
- \* Magnetically shielded.
- \* Stereo input.



### DESCRIPTION

The **RK1001** is a rack mount speaker using amplified multimedia speakers. The unit contains one input plug. The **RK1001** outputs 4 Watts and has a power switch and volume control behind the front panel door. The speakers are magnetically shielded for video and magnetic storage media protection. Color choice of light gray or black at no additional charge.

### SPECIFICATIONS

<b>Dimensions</b>	19.0" (W) x 3.5" (H) x 5.5" (D)
<b>Color</b>	Optional Black or Light Gray as photo above
<b>Weight</b>	4.3 pounds
<b>Output Power</b>	4W (1 KHz, 4 ohms @ 10% THD)
<b>Input Sensitivity</b>	200mV (1 KHz, 4 ohms @ 5W)
<b>Input Impedance</b>	25K ohms
<b>Frequency Response</b>	80Hz to 20KHz +/- 3dB
<b>Output Level</b>	0.45V (1 KHz, 30 ohms @ 200 mV input)
<b>Speaker Unit</b>	1.5" x 3.0" High Efficiency Drivers , magnetic shielding
<b>Power</b>	120VAC / 60Hz, 7.5VAC output

Specifications subject to change without notice.