


3-Phase 400V 32A basic PDU : C13 x 12 + C19 x 6



32A model :	Fuse	MCB
VP12C13/6C19-32A-CR_EN/2B-1	-	6

- Input Rating : 32A, 400V
 Inlet : 32A IEC60309 3P+N+E 6hr Red plug
 Cordset : 5-wire 2 meter 4mm sq. H07RN-F cordset
 Protection : 16A single pole hydraulic MCB x 6
 Bank Details : **PH-1** < **Bank 1** > Output 16A max. C 13 # 1-2 + C 19 # C 1
 < **Bank 2** > Output 16A max. C 13 # 3-4 + C 19 # C 2
PH-2 < **Bank 3** > Output 16A max. C 13 # 1-2 + C 19 # C 1
 < **Bank 4** > Output 16A max. C 13 # 3-4 + C 19 # C 2
PH-3 < **Bank 5** > Output 16A max. C 13 # 1-2 + C 19 # C 1
 < **Bank 6** > Output 16A max. C 13 # 3-4 + C 19 # C 2

Three phase basic PDU

Outlet : 10A Rated IEC320 C13 x 12
 16A Rated IEC320 C19 x 6



EMC Compliance : FCC & CE certified
 Safety Compliance : CE / LVD certified
 Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing

Dimension : 70 (W) x 83 (D) x 1425 (H) mm
 Material : Extrusion
 Color : Black