


LCD1U15-011/ 17-011/ 19-011 1U LCD Rackmount Drawer



Flip up design



Diagram

Unit : mm

Options:



AV Input



DVI Input



BNC Input



DC Power Input



Touch Screen

Designed for:



Drawer Features & Options

- 1U rackmount LCD drawer with either 15", 17" or 19" SAMSUNG LCD
- Multi lingual on screen display menu
- AV Composite Video, S-Video, DVI and BNC input options
- 12, 24 and 48 volt DC power options

LCD Drawer Benefits

- ▶ Sliding LCD allowing LCD to remain open when the rack door is closed

Monitor  Grade A industrial TFT LCD panel

- 15" 1024 x 768 LCD with 250 nit brightness and 700:1 contrast ratio typical
- 17" 1280 x 1024 LCD with 300 nit brightness and 1000:1 contrast ratio typical
- 19" 1280 x 1024 LCD with 300 nit brightness and 1000:1 contrast ratio typical

Ordering Information

15" LCD Series

17" LCD Series

19" LCD Series

| Model | LCD1U15-011 | LCD1U17-011 | LCD1U19-011 |
|-------|-------------|-------------|-------------|
|-------|-------------|-------------|-------------|

Dimensions

| Model | Product Dimension (W x D x H) | Net Weight |
|-------------|--|----------------|
| LCD1U15-011 | 442 x 550 x 44.2 mm 17.4 x 21.6 x 1.74 inch | 10 kg / 22 lbs |
| LCD1U17-011 | 442 x 550 x 44.2 mm 17.4 x 21.6 x 1.74 inch | 12 kg / 26 lbs |
| LCD1U19-011 | 442 x 600 x 44 mm 17.4 x 23.6 x 1.73 inch | 13 kg / 29 lbs |