



LCDR8U17-03/9U19-02/10U20-01 Rackmount LCD Quad Display

New



Front QD membrane button



DC 12V, 24V and 48V DC Power options

Display Features & Options

• 4 : 3, 17" in 8U, 19" in 9U or 20" in 10U

LCD Display Benefits




- ▶ Built-in Quad Display
- ▶ Ideal for CCTV security & industrial control

Monitor Grade A 17", 19" industrial TFT LCD panel

LG Grade A 20" industrial TFT LCD panel

- 17" 1280 x 1024 LCD with 300 nit brightness and 1000:1 contrast ratio typical
- 19" 1280 x 1024 LCD with 300 nit brightness and 1000:1 contrast ratio typical
- 20" 1600 x 1200 LCD with 300 nit brightness and 800:1 contrast ratio typical

Diagram Unit : mm



Ordering Information

17" LCD Series

19" LCD Series

20" LCD Series

Model	LCDR8U17-03	LCDR9U19-02	LCDR10U20-01
-------	-------------	-------------	--------------

Dimensions

Model	Product Dimension (W x D x H)	Net Weight
LCDR8U17-03	480 x 71.5 x 354.8 mm 18.9 x 2.8 x 14 inch	7 kg / 15 lbs
LCDR9U19-02	480 x 71.5 x 399 mm 18.9 x 2.8 x 15.7 inch	8 kg / 18 lbs
LCDR10U20-01	480 x 71.5 x 443 mm 18.9 x 2.8 x 17.4 inch	12 kg / 26 lbs