



禾瑞亞科技股份有限公司  
eGalax\_eMPIA Technology Inc.

EETI WinCE7 set registry document

## EETI WinCE7 set registry document for PCAP

Driver Registry Settings:

### 1. Settings for eetiTouchp.reg

The registry path :

[HKEY\_LOCAL\_MACHINE\Drivers\TouchKit]

Registry Key	Type	Default value	Description
CalSource	dword	1	CalSource = 0 for projected capacitive(Multi touch) touch device CalSource = 1 for resistive / surface capacitive / SAW/ IR touch device

### 2. If your touch device is PCAP with UART interface, you have to change the baud rate for support your PCAP device.

Settings for eeti232.reg

The registry path :

[HKEY\_LOCAL\_MACHINE\HARDWARE\DEVICEMAP\TOUCH]

Registry Key	Type	Default value	Description
Baud	dword	2580	Baud= 1C200. The baud rate is 115200 for supports projected capacitive EXC7900 series touch device. Baud= E100. The baud rate is 57600 for supports projected capacitive EXC7200 series touch device. Baud = 4B00 The baud rate is 19200 for supports projected capacitive EXC3000 series touch device. Baud= 2580.



禾瑞亞科技股份有限公司  
eGalax\_eMPIA Technology Inc.

#### EETI WinCE7 set registry document

			The baud rate is 9600 for supports resistive / surface capacitive / SAW/ IR touch device
--	--	--	--

Select the COM port which touch device is using, please modify eeti232.reg

[HKEY\_LOCAL\_MACHINE\Drivers\BuiltIn\TouchKit1]

"Dll"="TouchKit.dll"

"Order"=dword:FF

"Prefix"="TKT"

"Index"=dword:00000001

"Context"=dword:1; → This is the COM Port setting.

If touch device is connected to the COM2 , you have to set "Context"=dword:2