

1U Side-Access Rackmount LCD KVM Console Drawer | 26-inch Depth

Designed for compact 19-inch rack installations, this 1U slide-out LCD KVM console provides direct access to an integrated display, keyboard and pointing device. Choose a left-mounted or right-mounted console layout to suit space-limited workstations, rack aisles and control environments.



Key Features

- 1U, 19-inch rackmount side-access console
- Left- or right-mounted display/keyboard
- Side-access operation for confined spaces
- Configurable Power Input Panel Supporting Various Connector Types
- Welded aluminum chassis; C300 friction slides
- Integrated cable guidance system
- 12 VDC or 9-36 VDC power options

Configuration Options

- 17.3-inch FHD / UHD and 19-inch SXGA LCDs
- High-brightness and optically bonded panels
- Anti-reflective or anti-glare lens options
- Resistive or PCAP touchscreen options
- Keyboard and pointing device choices
- Optional integrated KVM switching
- Controller, latch and power-inlet selections

Specifications and available configurations vary by model. Contact Rackmount Mart for details.



KVM Switch Options



SD1: 4-port DisplayPort KVM switch



SE2u: 8-port VGA KVM switch



SG2x: 4-port DVI KVM switch



SO8: 8-port HDMI KVM switch



SIPx: 8 / 16 / 32-port RJ45 KVM switch

LCD Display Options

Model Number LCD1U19-38

19-inch SXGA | 1280 x 1024

350 nits | 1000:1 | 10 ms

Operating: -30°C to +85°C

Model Number LCD1U19-39

19-inch SXGA | 1280 x 1024

1600 nits | 1000:1 | 10 ms

Operating: -30°C to +70°C

Model Number LCD1U17-68

17.3-inch FHD | 1920 x 1080

400 nits | 600:1 | 40 ms

Operating: 0°C to +70°C

Model Number LCD1U17-69

17.3-inch FHD | 1920 x 1080

1000 nits | 600:1 | 40 ms

Operating: 0°C to +70°C

Model Number LCD1U17-70

17.3-inch UHD | 3840 x 2160

400 nits | 1000:1 | 27 ms

Operating: 0°C to +50°C

Keyboard Options



SQx: 97-key NEMA 4; touchpad

USB / PS2; 10M cycles



SA2x: 89-key; optical trackball

Cherry ML; 20M cycles



SI2u: 82-key; glide pad

Rubber membrane; 5M cycles



SHx: 113-key NEMA 4X; 3-button pointer

Silicone rubber; 10M cycles



SMx: 119-key; 3-button touchpad

Tactile ML; 50M operations

Configurations vary by display, input interface and application. Contact Rackmount Mart for availability.

LCD specifications are representative; configurations and availability may vary.