


# ID-46Pw-LED 46" High Resolution Widescreen LCD Panel w/ LED-backlit Display



## Display Benefits

- ▶ 46" widescreen LCD with **Full HD** 1080p resolution
- ▶ Green LED-backlit panel technology
- ▶ Rugged construction against external impact
- ▶ Standard with HDMI, DVI-D, VGA, S-Video, RCA, Audio & remote controller

## Options

- 3G / HD / SD-SDI Broadcast-grade input
- **MC** Multi-display control solution
- MIL-type or lockable connector
- TV - PAL or NTSC

Universal open frame mounting




Standard I/O : HDMI, DVI-D, Audio, S-Video, RCA, VGA

Options I/O : TV  
SDI or MC ( either one )

## Specifications

### • LCD Panel

Manufacturer :	
Size (diagonal) :	46" TFT
Max resolution :	1920 x 1080
Brightness (cd/m2) :	400
Backlight :	LED
Colors :	16.7 M
Contrast ratio (typ) :	4000 : 1
Viewing angle (H/V) :	178° x 178°
Active area (mm) :	1018 x 573
MTBF (hrs) :	30,000
Signal input :	HDMI / DVI-D / VGA / S-Video / RCA

### • Weight

Net : 50 kgs ( 110 lbs )

### • Mounting :

Universal mount

### • Environmental

Operating :	0 to 50°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5~90%, non-condensing
Shock :	10G acceleration ( 11 ms duration )
Vibration :	5~500Hz 1G RMS random vibration

### • Casing Color :

Dark grey ( RAL 7037 )

### • Regulatory :

FCC, CE

### • Power

Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 200 Watt, Standby 20 Watt

### • Dimensions

Product : 1117 x 74 x 672 mm / 44 x 3.1 x 26.5 inch

## Diagrams ( mm )

Front View

Side View

Rear View

