

# ID-H19Aw-LED 19" Front Aluminum Bezel Widescreen High Brightness LCD Display

NEMA 4 / IP65  
front protection




FC CE

## Display Benefits

- ▶ 19" widescreen LCD with high brightness 1000 cd/m<sup>2</sup>
- ▶ Green LED-backlit panel technology
- ▶ Rugged construction against external impact
- ▶ 6mm aluminum front bezel with protective glass

## Options

- HDMI, DVI-D, S-Video + BNC & Audio
- 3G / HD / SD-SDI Broadcast-grade input
- MC Multi-display control solution
- HW19" Touchscreen : Capacitive, Resistive, Multi-touch
- MIL-type or lockable connector
- 48V or 24VDC power
- TV - PAL or NTSC
- Auto / switch dimming



Standard I/O : VGA only

Options I/O : BNC + S-Video, Audio, TV, USB for touchscreen  
HDMI or DVI-D ( either one )

## Specifications

### • LCD Panel

Size (diagonal) :	19" TFT
Max resolution :	1440 x 900
Brightness (cd/m <sup>2</sup> ) :	1000
Backlight :	LED
Colors :	16.7 M
Contrast ratio (typ) :	1000 : 1
Viewing angle (H/V) :	160° x 160°
Active area (mm) :	408 x 255
MTBF (hrs) :	50,000
Signal input :	VGA

### • Weight

Net : 5 kgs ( 11 lbs )

### • Mounting :

Panel mount / VESA mount

### • Environmental

Operating :	0 to 50°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5~90%, non-condensing
Shock :	10G acceleration ( 11 ms duration )
Vibration :	5~500Hz 1G RMS random vibration

### • Casing Color :

Black front panel ( RAL 9005 )  
Dark grey rear case ( RAL 7037 )

### • Regulatory :

FCC, CE

### • Power

Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 84 Watt, Standby 5 Watt

### • Dimensions

Product : 509 x 66 x 338 mm / 20 x 2.6 x 13.3 inch

## Diagrams ( mm )

