

ID-32Pw 32" Widescreen Open Frame LCD Panel Display

Universal open frame mounting




Display Benefits

- ▶ 32" widescreen LCD with high resolution 1366 x 768
- ▶ Rugged construction against external impact
- ▶ Standard with HDMI, VGA, S-Video, RCA, Audio & remote controller

Options

- TV - Analog

Basic I/O



Specifications

• LCD Panel

Manufacturer :	
Size (diagonal) :	32" Widescreen TFT
Max resolution :	1366 x 768
Brightness (cd/m2) :	450
Backlight :	CCFL
Colors :	16.7 M
Contrast ratio (typ) :	5000 : 1
Viewing angle (H/V) :	178° x 178°
Active area (mm) :	698 x 392
MTBF (hrs) :	50,000
Signal input :	HDMI / VGA / S-Video / RCA

• Weight

Net : 16.9 kgs (37.2 lbs)

• Mounting :

Universal mount / VESA mount

• Environmental

Operating :	0 to 50°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5-90%, non-condensing
Shock :	10G acceleration (11 ms duration)
Vibration :	5-500Hz 1G RMS random vibration

• Casing Color :

Black (RAL 9005)

• Regulatory

Safety :	FCC & CE certified
Environmental :	RoHS2 & REACH compliant

• Power


Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 200 Watt, Standby 20 Watt

• Dimensions


Product : 836 x 117.3 x 510 mm / 32.9 x 4.6 x 20.1 inch

Diagrams (mm)

Front View



Side View



Rear View

