


3-Phase 400V 16A monitored PDU + outlet measurement : C13 x 12 + C19 x 12



16A model :	Fuse	MCB
VP12C13/12C19-16A-Wi/F_EN/2B-2/LOCK	3	-
VP12C13/12C19-16A-Wi/CR_EN/2B-2/LOCK	-	3

- Input Rating : 16A, 400V
- Inlet : 16A IEC60309 3P+N+E 6hr Red plug
- Cordset : 5-wire 2 meter 1.5mm sq. H07RN-F cordset
- Protection : 16A resettable fuse or 16A single pole hydraulic MCB x 3
- Phase Details : < PH-1 > Output 16A max. C 13 # 1 - 4 + C 19 # C 1 - C 4
< PH-2 > Output 16A max. C 13 # 1 - 4 + C 19 # C 1 - C 4
< PH-3 > Output 16A max. C 13 # 1 - 4 + C 19 # C 1 - C 4

Three phase monitored PDU + outlet measurement

Outlet : 10A Rated IEC320 C13 (lockable) x 12
16A Rated IEC320 C19 (lockable) x 12

Meter Features (Wi Monitored PDU + Outlet Measurement)

Local Display : Field replaceable 1.8" color LCD
Bank Measurement : Current (A), Energy (kWh), Voltage (V) & Power factor
Outlet Measurement : Current (A), Energy (kWh)
Accuracy : ±1% true RMS
IP Access : via IP dongle, one IP Access up to 16 PDU Levels
Cascade : Up to 16 PDU under single IP address via IP dongle
SNMP : via IP dongle
Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC & CE certified
Safety Compliance : CE / LVD cekb2rtified
Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C
Storage Temperature : -25 to 65 °C
Operating Altitude : 0 to 2,000 m
Storage Altitude : 0 to 15,000 m
Humidity : 8 to 95% RH, non-condensing

Dimension : 100 (W) x 90 (D) x 1325 (H) mm
Material : Steel
Color : White (outlet bracket)
Black (chassis)

Synergy Global Technology Inc
www.RackmountMart.com