



6mm aluminum front bezel with optional

NEMA 4 / IP65 front protection



Display Benefits

- ▶ 12.1" LCD with resolution 800 x 600
- ▶ Green LED-backlit panel technology
- ▶ Rugged construction against external impact
- ▶ Protective 3mm glass
- ▶ 6mm aluminum front bezel with protective glass (Optional)


Options

- S-Video + BNC & Audio
- 48V, 24V or 12VDC power
- 12.1" Touchscreen : Capacitive, Resistive
- TV - Analog

Standard I/O



BNC-SPK upgrade I/O



Specifications

• LCD Panel

Manufacturer :	AUO
Size (diagonal) :	12.1" TFT
Max resolution :	800 x 600
Brightness (cd/m2) :	450
Backlight :	LED
Colors :	262 K
Contrast ratio (typ) :	700 : 1
Viewing angle (H/V) :	160° x 140°
Active area (mm) :	246 x 185
MTBF (hrs) :	50,000
Signal input :	VGA

• Weight

Net : 3 kgs (6.6 lbs)

• Mounting :

Panel mount / VESA mount

• Environmental

Operating :	0 to 50°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5~90%, non-condensing
Shock :	10G acceleration (11 ms duration)
Vibration :	5~500Hz 1G RMS random vibration

• Casing Color :

Black front panel (RAL 9005)
Dark grey rear case (RAL 7037)

• Regulatory :

FCC, CE

• Power


Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 40 Watt, Standby 5 Watt

• Dimensions


Product : 345 x 68 x 256 mm / 13.6 x 2.7 x 10.1 inch

Diagrams (mm)

Front View



Side View



Rear View

