



Universal open frame mounting



Display Benefits

- ▶ 12.1" LCD with resolution 800 x 600
- ▶ Green LED-backlit panel technology
- ▶ Rugged construction against external impact


Options

- S-Video + BNC & Audio
- 12.1" Touchscreen : Capacitive, Resistive
- 48V, 24V or 12VDC power
- TV - Analog

Standard I/O



BNC-SPK upgrade I/O



Specifications

• **LCD Panel**

Manufacturer :	AUO
Size (diagonal) :	12.1" TFT
Max resolution :	800 x 600
Brightness (cd/m2) :	450
Backlight :	LED
Colors :	262 K
Contrast ratio (typ) :	700 : 1
Viewing angle (H/V) :	160° x 140°
Active area (mm) :	246 x 185
MTBF (hrs) :	50,000
Signal input :	VGA

• **Weight**

Net : 3 kgs (6.6 lbs)

• **Mounting :** Universal mount / VESA mount

• **Environmental**

Operating :	0 to 50°C Degree
Storage :	-5 to 60°C Degree
Relative humidity :	5~90%, non-condensing
Shock :	10G acceleration (11 ms duration)
Vibration :	5~500Hz 1G RMS random vibration

• **Casing Color :** Dark grey (RAL 7037)

• **Regulatory :** FCC, CE


• **Power**

Input :	Auto-sensing 100 to 240VAC, 50 / 60Hz
Consumption :	Max. 40 Watt, Standby 5 Watt

• **Dimensions**

Product : 342 x 62 x 253 mm / 13.5 x 2.5 x 10 inch

Diagrams (mm)



Side View



Rear View

