



**Product # :** WK1002

**Product Name :** 19" Rackmount LCD Chassis (6U)

**Weight :** 25 lb / 11.4kg

**Dimension :** 19" (W) x 12" (D) x 10.4" (H)  
483 (W) x 305 (D) x 265.9 (H) mm

**Product Description:**

19" LCD Rackmount Workstation

**Product Features:**

- \* NEMA 4 (IP56) / NEMA 12 (IP52) for front panel
- \* 12.1" TFT LCD display, 800x600 resolutions
- \* Drive space: 3 x 5.25" FDD
  - 1 x 3.5" FDD
  - 1 x 3.5" HDD
- \* Built-in 3 x 37cm cooling fans inside (flow in), and 1 x 8cm fan (flow out)
- \* Expansion slots: 14-slot PCI/ISA passive backplane, or baby AT or ATX main board
- \* Power supplies for optional:
  - PS/2 type 250W ~ 400W power supply
  - 250W ~ 350W ATX power supply
  - 250W hot-swap redundant power supply
  - 250W hot-swap redundant ATX power supply
  - 300W hot-swap redundant power supply

**Optional:**

-Touch screen