



1U Rackmount keyboard drawer with KVM series



Matrix KVM 8, 16, 32 port button



PS/2 KVM 4, 8, 16 port button



Combo KVM 8, 16, 32 port button



KVM Options

- Multi-user Matrix Cat6 KVM with either 16 or 32 ports in 1U
- Cost efficient Combo KVM integration
- Mix PS/2 & USB with multi-platform switch capability
- Secure remote user access across the world wide web

Keyboard Drawer Benefits

- ▶ Enhanced aesthetics with new molded front panel and two point lock
- ▶ Combo interface either PS/2 or USB input
- ▶ Multiple keyboard language selections with touchpad or trackball

Dimensions

Model	Product Dimension (W x D x H)	Net Weight
See page 2	442 x 550 x 44 mm 17.4 x 21.6 x 1.73 inch	8 kg / 18 lbs

Keyboard Selection

Supporting layouts



Ne N keyboard with touchpad



Nb N keyboard with trackball



d Compact keyboard with trackball



t Compact keyboard with touchpad mouse

KVM Selection







Base Model







Keyboard Drawer Series









<ul style="list-style-type: none"> * Single port w/o KVM * Combo interface 	LCDK1002
--	-----------------







Matrix Cat6 KVM

	2 consoles	Matrix Cat6 16 port	LCDK1065-2
	3 consoles		LCDK1065-3
	4 consoles		LCDK1065-4
IP 	3 consoles	Matrix IP Cat6 16 port	LCDK1068-31
IP 	4 consoles		LCDK1068-41
IP IP 	4 consoles		LCDK1068-42










	2 consoles	Matrix Cat6 32 port	LCDK1067-2
	3 consoles		LCDK1067-3
	4 consoles		LCDK1067-4
IP 	3 consoles	Matrix IP Cat6 32 port	LCDK1069-31
IP 	4 consoles		LCDK1069-41
IP IP 	4 consoles		LCDK1069-42

Matrix DB-15 KVM







	2 consoles	Matrix DB-15 8 port	LCDK1061-2
	3 consoles		LCDK1061-3
	4 consoles		LCDK1061-4
IP 	3 consoles	Matrix IP DB-15 8 port	LCDK1063-31
IP 	4 consoles		LCDK1063-41
IP IP 	4 consoles		LCDK1063-42

	2 consoles	Matrix DB-15 16 port	LCDK1062-2
	3 consoles		LCDK1062-3
	4 consoles		LCDK1062-4
IP 	3 consoles	Matrix IP DB-15 16 port	LCDK1064-31
IP 	4 consoles		LCDK1064-41
IP IP 	4 consoles		LCDK1064-42



Combo Cat6 KVM

	1 console	Combo Cat6 8 port	LCDK1050
	2 consoles		LCDK1055
IP 	2 consoles		LCDK1058
	1 console	Combo Cat6 16 port	LCDK1051
	2 consoles		LCDK1056
IP 	2 consoles		LCDK1059
	1 console	Combo Cat6 32 port	LCDK1052
	2 consoles		LCDK1057
IP 	2 consoles		LCDK1060

Combo DB-15 KVM

	1 console	Combo DB-15 8 port	LCDK1027
	2 consoles		LCDK1029
IP 	2 consoles		LCDK1053
	1 console	Combo DB-15 16 port	LCDK1028
	2 consoles		LCDK1030
IP 	2 consoles		LCDK1054

PS/2 DB-15 KVM

	1 console	4 port	LCDK1003
		 DB-15 8 port	LCDK1004
		16 port	LCDK1017