

45U AV Rack Cabinet - 32" deep

45 RU Pre-Configured BGR for AV Systems - 32 Inches Deep **SKU: BGR-4532-AV**



A pre-configured BGR built for today's AV systems. The accessories and options included with the Pre-Configured BGR for AV are exactly what you need to deliver an optimized AV system. It includes some of our most popular Forward accessories as well as thermal management and cable management.

The AV Pre-Configured BGR Includes:

Included Forward Panels

- (4) Forward 1RU flanged blank panels (FWD-EB1)
- (2) Forward 2RU flanged blank panels (FWD-EB2)

Included Horizontal Cable Management:

- (1) 4pk of Forward straight horizontal lacer bar (FWD-LB-1A-4PK)
- (1) 4pk of Forward 2" offset horizontal lacer bar (FWD-LB-2A-4PK)

Included Vertical Cable Management:

- (1) Forward Vertical Wire Grid Lace for vertical and horizontal cable routing on a single lace bar (FWD-LACE-WB3-44-45)
- (1) Forward Vertical Cable Management Lace (FWD-LACE-UMV-44-45) with the patented universal hole pattern. Compliment with FWD-C-RING, FWD-D-RING and FWD-TSW-15
- (2) Lever Lock™ vertical channel (LL-VC21)

Included Cable Management Accessories:

- (1) 15pk of Forward tie saddles for optimal cable management in any direction using absolutely no hardware. Accepts both cable zip ties and hook & loop. (FWD-TSW-15)
- (2) Velcro® straps for tie saddles (TW12)

Included Small Device Mounting:

45U AV Rack Cabinet - 32" deep

- (2) 4pk of Forward small device clamps for quick mounting of small, non-rackmount devices without any hardware (FWD-SIDECLMP-4)
- (1) Lever Lock™ plate for small device mounting (LL-VP2110)

Included Thermal Management:

- (1) DC fan top with 4 fans moving 276CFM. Includes controller and plugs for North America, EU, UK and Australia (IBGR-276FT-FC)

Included Rack Options:

- (1) Solid front door (BFD-45)
- (1) Pair of side panels (BSPN-45-32)
- (1) set of leveling feet (LF-HD)

Included Hardware:

- (100) 10-32 threaded rackscrews (HP)

Specifications

Dimensions & Measurements

CFM	276
Depth	32 in (81.3 cm)
Height	83.23 in (211.4 cm)
Panel Width	19 in (48.3 cm)
Rack Units	45 RU
Shipping Weight	320 lbs (145.2 kg)
Usable Depth	22.9 in (58.2 cm)
Usable Height	78.88 in (200.4 cm)
Weight Capacity	3000 lbs (1360.8 kg)
Width	23 in (58.4 cm)

45U AV Rack Cabinet - 32" deep

Characteristics & Features

Color	Black
Finish	Black Wrinkle Powder Coat
Forward Compatible	Yes
Gangable	Yes
Handles	25mm x 150mm Swing Handle
Material	Steel
Product Configuration	Pre-Configured for Pro AV
Rack Rail Type	Forward Rackrail
Rack Type	Pre-Configured
Rear Door	Yes
Special Features	Installation Time Savers
UPC	656747384431