


ID-H17D 17" SunReadable Stylish Front Aluminum Cover LCD Panel

Dimension Drawings (mm)



Applications

- Industrial process control
- Point of sales / Kiosk
- Security / Surveillance
- Touchscreen display panel

Options

- Touchscreen
- S-Video, RCA & BNC & DVI
- DC power input (12 / 24 / 48 VDC)
- Audio input with speaker
- TV tuner with remote controller
- Standard remote controller for AV, VGA, DVI input

Design features

- SunReadable LCD panel
- 800 cd/m² industrial brightness
- 1.2mm aluminum front cover
- OSD control keys to optimize the display

Specifications

LCD Panel



Panel Grading	Class A TFT LCD panel
Panel Size (in.)	17"
Optimum Resolution	1280 x 1024
Display Color	16.2M
Brightness-nits (cd/m ²)	800
Contrast Ratio	500 : 1
Pixel Pitch (mm)	0.264 x 0.264
Viewing Angle (L/R/U/D)	70 / 70 / 70 / 60
OSD Control	Brightness, Contrast, Phase & Clock, Color, H & V position, Auto-tune & Recall
Connector(s)	D-Sub 15 pin VGA analog
LCD Panel MTBF (hrs)	50,000
Power	100~240VAC via AC adapter
Mounting	VESA-mount, Optional OEM mounting design
Dimensions (mm)	393 x 52 x 311 (W x D x H)

Operating Temperature	0° to 50° C
Storage Temperature	-5° to 60° C
Humidity	5~90%, non-condensing
Shock	10G peak acceleration (11ms duration)
Vibration	5-500Hz, 1G RMS random vibration

Ordering information

Model no.	Description
ID-H17D	17" SunReadable front aluminum cover LCD w/ VGA input
ID-H17DAV	17" SunReadable front Al. cover LCD w/ VGA,S-Video+RCA input
ID-H17DDVI	17" SunReadable front Al. cover LCD w/ VGA, DVI input
ID-H17DBNC	17" SunReadable front Al. cover LCD w/ VGA,S-Video+BNC input
ID-H17DDC12	17" SunReadable front Al. cover LCD w/ VGA input, 12V DC input
ID-H17DDC24	17" SunReadable front Al. cover LCD w/ VGA input, 24V DC input
ID-H17DDC48	17" SunReadable front Al. cover LCD w/ VGA input, 48V DC input